





FAPROSID s.r.l
PRODOTTI SIDERURGICI

**BEFORE
MOULDING**





**AFTER
MOULDING**



Depending on the moulding line, customers may need to lower the pin further (dimension A) to obtain a position as close as possible to the piece after moulding.



FAPROSID s.r.l
 PRODOTTI SIDERURGICI



TYPE **MTF**

TYPE	DIMENSIONS						
	H	A	B	C	D	D1	D2
MTF10	90	35	20	35	4	14	20
MTF16	110	60	20	30	7,1	4	20
MTF22	110	60	20	30	7	14	20
MTF29	135	70	20	45	6	16	22
MTF30	130	60	20	50	7,1	6	22
MTF32	130	50	20	60	7	14	20
MTF34	120	50	20	50	7	16	22
MTF39	155	60	20	75	6	16	22
MTF50	130	60	20	50	6,5	19	25
MTF75	120	60	20	40	7	19	25
MTF76	150	60	20	70	7,5	19	25
MTF82	140	60	30	50	7	19	25
MTF89	140	60	30	50	8	19	25
MTF115	155	60	30	65	10	18	24
MTF133	145	65	30	50	7,5	18	24
MTF153	150	65	30	55	9,5	19	25
MTF185	170	60	30	80	8	29	35
MTF232	155	65	30	60	10	29	35
MTF234	235	70	30	135	8	19	25
MTF261	140	60	30	50	7,5	24 /29	30
MTF270	170	60	30	80	9,5	24 /29	30
MTF333	180	70	30	80	11	24 /29	30
MTF409	235	80	30	125	10	25/29	31
MTF474	210	90	30	90	10	40	46
MTF584	180	70	30	80	11	25/29	31
MTF674	220	80	30	110	10	25/29	31
MTF764	240	90	30	120	15	25/29	31
MTF774	240	100	30	110	15	29	34

Depending on the moulding line, customers may need to lower the pin further to obtain a position as close as possible to the moulded piece.