




# BRECHKERN AUS SILICIUMDIOXID, SILICIUMDIOXID/MAGNETIT UND MULLIT



TYP

**A**

| TYP  | D mm | H mm | C mm | V mm |
|------|------|------|------|------|
| A100 | 110  | 11   | 50   | 5    |
| A110 | 136  | 11   | 55   | 5    |
| A120 | 150  | 14   | 55   | 5    |
| A130 | 160  | 15   | 60   | 5    |
| A140 | 170  | 14   | 68   | 5    |
| A150 | 180  | 14   | 75   | 5    |
| A160 | 200  | 14   | 80   | 5    |
| A180 | 212  | 16   | 85   | 5    |
| A200 | 235  | 16   | 90   | 5    |
| A220 | 255  | 16   | 100  | 5    |
| A250 | 290  | 16   | 110  | 5    |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |
|      |      |      |      |      |

Ausgabedatum  
JULI 2015

Genehmigung der  
Geschäftsleitung

## TOLERANZEN

| D      | H      | C      | V      |
|--------|--------|--------|--------|
| ± 2 mm | ± 2 mm | ± 2 mm | ± 1 mm |