



# BRECHKERN AUS BLECH

TYP **MTF**



| TYP    | D mm. | A mm. | C mm. | H mm. | E cm2 |
|--------|-------|-------|-------|-------|-------|
| MTF10  | 38    | 25    | 15    | 8     | 1,80  |
| MTF16  | 38    | 25    | 15    | 8     | 1,80  |
| MTF22  | 38    | 25    | 15    | 8     | 1,80  |
| MTF29  | 52    | 35    | 17    | 11    | 2,30  |
| MTF30  | 52    | 35    | 17    | 11    | 2,30  |
| MTF32  | 38    | 25    | 15    | 8     | 1,80  |
| MTF34  | 52    | 35    | 17    | 11    | 2,30  |
| MTF39  | 52    | 35    | 17    | 11    | 2,30  |
| MTF50  | 58    | 38    | 20    | 12    | 3,10  |
| MTF75  | 58    | 38    | 20    | 12    | 3,10  |
| MTF76  | 68    | 36    | 20    | 15    | 3,10  |
| MTF82  | 58    | 38    | 20    | 12    | 3,10  |
| MTF89  | 80    | 56    | 20    | 12    | 3,50  |
| MTF115 | 64    | 38    | 19    | 10    | 2,80  |
| MTF133 | 64    | 38    | 19    | 10    | 2,80  |
| MTF153 | 80    | 56    | 20    | 12    | 3,50  |
| MTF185 | 88    | 60    | 30    | 12    | 4,90  |
| MTF232 | 88    | 60    | 30    | 12    | 4,90  |
| MTF234 | 80    | 56    | 20    | 12    | 3,50  |
| MTF261 | 96    | 66    | 25/30 | 13    | 4,90  |
| MTF270 | 96    | 66    | 25    | 13    | 4,90  |
| MTF333 | 96    | 66    | 25    | 13    | 4,90  |
| MTF409 | 108   | 70    | 26/30 | 18    | 5,30  |
| MTF474 | 126   | 80    | 41    | 16    | 13,20 |
| MTF584 | 108   | 70    | 26/30 | 18    | 5,30  |
| MTF674 | 108   | 70    | 26/30 | 18    | 5,30  |
| MTF764 | 108   | 70    | 26/30 | 18    | 5,30  |
| MTF774 | 126   | 80    | 29    | 18    | 6,60  |

Ausgabedatum  
JULI 2015

Genehmigung der  
Geschäftsleitung

## TOLERANZEN

| D      | A      | C      | H      |
|--------|--------|--------|--------|
| ± 1 mm | ± 1 mm | ± 1 mm | ± 1 mm |



E\* = Brechbereich

